




## HELISLOT side milling cutter without flange, $\varnothing$ DC / Zeff: 160/18mm



### Order data

Order number	227722 160/18
GTIN	7291075430806
Item class	19D

### Description

#### Version:

Economical machining of grooves and T-slots. Achieve different slot widths with only one insert size thanks to the insert seat concept with staggered teeth formation. Square inserts with positive rake angle for efficient and gentle machining. Very reliable process thanks to optimised insert support in the seat.

#### Spare part:

Pack of insert screws No. **229695 3** (TX9; 2.0 Nm).

### Technical description

Number of effective inserts $Z_{\text{eff}}$	18
Number of indexable inserts	18
Mounting bore $\varnothing$	40 mm
Series	HELISLOT
Overall length $L_{\text{tot}}$	14 mm
maximum cutting depth $a_{\text{e,max}}$	51 mm

Cutting edge $\varnothing D_c$	160 mm
Slot width $a_p$	10 mm
Manufacturer's designation	SDN D160-10-40-XN09
Shank type	with bore
Type of product	Side milling cutter

---

## Accessories

Set of insert screws 5 pieces Type 3	229695 3
--------------------------------------	----------