



PENTACUT PCH 24-34 toolholder, right-hand, Shank size / insert size: 12/24mm



Order data

Order number	273924 12/24
GTIN	7291075172010
Item class	26D

Description

Suitable for:

Inserts No. 273937 – 273939.

Technical description

Grooving depth t_{max}	6.5 mm
Shank size	12 mm
Head length L_1	19.5 mm
Series	PENTACUT
Overall length L	120 mm
HBH	4 mm
CWN-CWX	0.5 - 3.2 mm
Insert size	25 mm
Manufacturer's designation	PCHR 12-24
Application type	right-hand
Through-coolant	no
axial grooving possible	no
Type of product	Screw-on toolholder

