



PENTACUT PCH 24-34 toolholder, right-hand, Shank size / insert size: 25/34mm



Order data

| | |
|--------------|---------------|
| Order number | 273924 25/34 |
| GTIN | 7291075287110 |
| Item class | 26D |

Description

Suitable for:

Inserts No. 273937 – 273939.

Technical description

| | |
|----------------------------|---------------------|
| Grooving depth t_{max} | 10 mm |
| Shank size | 25 mm |
| Series | PENTACUT |
| Overall length L | 135 mm |
| Head length L_1 | 31 mm |
| CWN-CWX | 1.5 - 4 mm |
| Manufacturer's designation | PCHR 25-34 |
| Application type | right-hand |
| Through-coolant | no |
| axial grooving possible | no |
| Type of product | Screw-on toolholder |

