




XNMU 130608PNTN, IC810, Type: GGG



Order data

Order number	227746 GGG
GTIN	7291075311280
Item class	19A

Description

Version:

Double-sided indexable insert with 8 helical cutting edges. Very robust design, special insert thickness. Very reliable process due to positive installation position in the insert seat. Excellent chip control and evacuation.

Note:

Standard application values for a_e max

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

ISO code indexable insert	XNMU 130608PNTN
Series	HELISLOT
Type	GGG
Feed f_z	0.15 mm
Geometry	PNTN
Manufacturer's designation	XNMU 130608PNTN IC810

Grade	IC810
Tool material	Carbide
Type of product	Indexable insert for milling

User data

	Suitability	V_c	ISO code
GG	suitable only under restricted conditions	300 m/min	K
GGG	suitable	240 m/min	K
wet maximum	suitable		
dry	suitable		