



MINCUT boring bar, right-hand, Shank \varnothing / insert size: 16/15mm



Order data

Order number	270420 16/15
GTIN	7291075262421
Item class	26l

Description

Version:

- Carbide insert screwed on to the end face, positive force transmission due to end face serrations.
- Insert change is very easy to perform.

Application:

For face grooving and groove turning in the diameter range 8 mm – 17 mm.

Suitable for:

Inserts No. 270422 – 270429.

Technical description

Shank \varnothing D _s	16 mm
Overall length L	100 mm
Series	MINCUT
Centre offset L ₃	12.5 mm
Insert size	15 mm
Head length l ₂	19 mm
Function width f ₁	2.7 mm
Radial width f ₂	7.5 mm
Cooling \varnothing d _s	8 mm
Radius R	10.3 mm

Manufacturer's designation	MIFHR 16C-15
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar