


**CCMT 09T308, Grade: IC807****Order data**

Order number	260172 IC807
GTIN	7291075351910
Item class	26B

**Description****Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

ISO code indexable insert	CCMT 09T308
Cutting depth $a_p$	0.5 - 4 mm
Finishing/roughing assignment	Finishing
Cutting speed $v_c$ main application	50 - 245 m/min
Series	ISOTURN
Grade	IC807
Chip breaker	M3P
Corner radius	0.8 mm
Main application	P

Tool material	Carbide
Number of changes/inserts	2
Feed f	0.08 - 0.3 mm/rev.
Cutting conditions	slightly interrupted
Manufacturer's designation	CCMT 09T308-M3P IC807
Type of product	Indexable insert for turning