


**CCMT 09T304, Grade: IC807****Order data**

Order number	260171 IC807
GTIN	7291075423877
Item class	26B

Description**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Finishing/roughing assignment	Finishing
Main application	M
Cutting conditions	slightly interrupted
Cutting speed v_c main application	30 - 80 m/min
Chip breaker	M3M
Grade	IC807
ISO code indexable insert	CCMT 09T304
Cutting depth a_p	0.5 - 4 mm
Corner radius	0.4 mm

Series	ISOTURN
Feed f	0.08 - 0.3 mm/rev.
Manufacturer's designation	CCMT 09T304-M3M IC807
Type of product	Indexable insert for turning