



CCMT 09T304, Grade: IC807

Order data

Order number	260102 IC807
GTIN	7291075337969
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Cutting depth a_p	0.1 - 2 mm
Grade	IC807
Feed f	0.06 - 0.25 mm/rev.
Series	ISOTURN
Corner radius	0.4 mm
ISO code indexable insert	CCMT 09T304
Main application	P
Chip breaker	F3P
Cutting speed v_c main application	50 - 245 m/min

Cutting conditions	continuous
Finishing/roughing assignment	Finishing
Manufacturer's designation	CCMT 09T304-F3P IC807
Type of product	Indexable insert for turning