


DCMT 11T304, Grade: IC807

Order data

Order number	260510 IC807
GTIN	7291075485882
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Number of changes/inserts	2
Cutting speed v_c main application	50 - 245 m/min
Cutting depth a_p	0.8 - 3 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Corner radius	0.4 mm
Cutting conditions	slightly interrupted
Main application	P
Grade	IC807

ISO code indexable insert	DCMT 11T304
Chip breaker	M3P
Feed f	0.1 - 0.3 mm/rev.
Series	ISOTURN
Manufacturer's designation	DCMT 11T304-M3P IC807
Type of product	Indexable insert for turning