

**DCMT 11T308, Grade: IC807****Order data**

| | |
|--------------|---------------|
| Order number | 260513 IC807 |
| GTIN | 7291075423778 |
| Item class | 26B |

Description**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|--------------------------------------|-------------------|
| Cutting speed v_c main application | 30 - 80 m/min |
| Cutting depth a_p | 0.8 - 3 mm |
| Number of changes/inserts | 2 |
| ISO code indexable insert | DCMT 11T308 |
| Main application | M |
| Finishing/roughing assignment | Finishing |
| Chip breaker | M3M |
| Feed f | 0.1 - 0.3 mm/rev. |
| Corner radius | 0.8 mm |

| | |
|----------------------------|------------------------------|
| Tool material | Carbide |
| Grade | IC807 |
| Series | ISOTURN |
| Cutting conditions | slightly interrupted |
| Manufacturer's designation | DCMT 11T308-M3M IC807 |
| Type of product | Indexable insert for turning |