



DNMG 150604, Grade: IC6025



Order data

Order number	250730 IC6025
GTIN	7291075341898
Item class	26B

Description

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Chip breaker	F3M
Number of changes/inserts	4
Tool material	Carbide
Cutting depth a_p	0.1 - 1.5 mm
Cutting conditions	slightly interrupted
Grade	IC6025
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	120 - 230 m/min
Feed f	0.1 - 0.4 mm/rev.

ISO code indexable insert	DNMG 150604
Main application	M
Corner radius	0.4 mm
Manufacturer's designation	DNMG 150604-F3M IC6025
Type of product	Indexable insert for turning