


DNMG 150612, Grade: IC8150

Order data

Order number	250811 IC8150
GTIN	7291075329858
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Cutting depth a_p	0.5 - 5 mm
Feed f	0.15 - 0.6 mm/rev.
Corner radius	1.2 mm
Cutting conditions	continuous
Cutting speed v_c main application	180 - 400 m/min
Number of changes/inserts	4
ISO code indexable insert	DNMG 150612
Tool material	Carbide
Main application	P

Finishing/roughing assignment	Finishing
Grade	IC8150
Chip breaker	M3P
Manufacturer's designation	DNMG 150612-M3P IC8150
Type of product	Indexable insert for turning