


DNMG 150608, Grade: IC6015

Order data

Order number	250810 IC6015
GTIN	7291075305111
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Grade	IC6015
Cutting speed v_c main application	140 - 300 m/min
ISO code indexable insert	DNMG 150608
Chip breaker	M3M
Corner radius	0.8 mm
Cutting conditions	continuous
Tool material	Carbide
Number of changes/inserts	4
Finishing/roughing assignment	Finishing

Feed f	0.17 - 0.5 mm/rev.
Main application	M
Cutting depth a_p	0.5 - 5 mm
Manufacturer's designation	DNMG 150608-M3M IC6015
Type of product	Indexable insert for turning