


DNMG 150608, Grade: IC8150

Order data

Order number	250810 IC8150
GTIN	7291075329841
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Feed f	0.15 - 0.6 mm/rev.
Cutting conditions	continuous
Chip breaker	M3P
Grade	IC8150
Corner radius	0.8 mm
Cutting depth a_p	0.5 - 5 mm
Tool material	Carbide
Cutting speed v_c main application	180 - 400 m/min
Number of changes/inserts	4

ISO code indexable insert	DNMG 150608
Main application	P
Finishing/roughing assignment	Finishing
Manufacturer's designation	DNMG 150608-M3P IC8150
Type of product	Indexable insert for turning