



DNMG 150608, Grade: IC6015



Order data

Order number	250731 IC6015
GTIN	7291075341904
Item class	26B

Description

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Chip breaker	F3M
Cutting speed v_c main application	140 - 300 m/min
Cutting depth a_p	0.1 - 1.5 mm
Cutting conditions	continuous
ISO code indexable insert	DNMG 150608
Number of changes/inserts	4
Feed f	0.1 - 0.4 mm/rev.
Tool material	Carbide
Grade	IC6015

Finishing/roughing assignment	Finishing
Main application	M
Corner radius	0.8 mm
Manufacturer's designation	DNMG 150608-F3M IC6015
Type of product	Indexable insert for turning