

## Garant

### GARANT Softcut® 90° shoulder mill MTC long, Plain shank, Ø D / number of teeth Z: 16/3mm



#### Order data

Order number	215609 16/3
GTIN	4045197409836
Item class	210

#### Description

##### Version:

High precision indexable face mill with irregular pitch for very smooth cutting, very high precision and very high metal removal rate. **New generation** of high performance indexable face mills **with special geometry for reduced cutting forces for MTC applications** under **unstable conditions** or **for spindles with low drive power. Suitable inserts APMT 0602..**

##### Application:

For shoulder milling to large depths, also slotting. General use in all steels including stainless and acid-resistant steels.

##### Spare part:

Pack of insert screws No. 219827 (6IP; 0.45 Nm).

##### Note:

GARANT torque screwdriver TQ No. **211750 size 0.45**, use bit No. **674252 size 6IP**.

The insert pocket must be modified when using indexable inserts with a radius of 2 mm.

#### Technical description

Overall length $L_{tot}$	90 mm
Pack of insert screws	219827 (6IP; 0.45 Nm)
Shank $\varnothing D_s$ , h6	16 mm
suitable indexable insert	AP.. 0602..
Overhang $L_1$	20 mm
Cutting edge $\varnothing D_c$	16 mm

Number of cutting edges Z	3
Ramping length L for $\alpha_{\max}$	12.85 mm
Circular interpolation milling $\varnothing D_{\max}$	30 mm
Circular interpolation milling $\varnothing D_{\min}$	30 mm
Circular interpolation milling $a_p$	0.9 mm
Ramping angle $\alpha_{\max}$	0.89 degrees
Series	Softcut®
$\varnothing D_3$	14 mm
Shank type	Plain shank
Setting angle $\kappa$	90 degrees
Milling application	End milling
Milling application	Ramping
Milling application	Circular milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	End / face mill

## Accessories

Set of insert screws 10-piece	219827
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 6IP	674252 6IP
Torque screwdriver, fixed setting set torque 0,45 N·m	211750 0,45