

 Mahr**Digital caliper MarCal without measuring tips, Measuring range: 800mm****Order data**

Order number	415322 800
GTIN	4059192064778
Item class	43A

**Description****Version:**

**Direct reading from large and clear digital display. Precision lapped measuring faces.** The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size CR2032

**Optional extras:**

Data cable No. 498940.

**Technical description**

Scale divisions	0.01 mm
Calibration	A1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Jaw length	150 mm
Wireless application	Manufacturer's software
Number of batteries contained	1
Scale divisions	0.0005 in

IP Index of Protection	IP 65
Reversible reading	mm / inch
Internal jaw Ø	20 mm
Measuring range	0 - 800 mm
Error limit	0.05 mm
Power supply	Battery-powered
Standard	Works standard
Interface	USB interface
Interface	Digimatic interface
Interface	RS232 interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

## Services

DAkKS calibration Calipers / depth gauges maximum measuring range 1000 mm	021010 1000
Calibration Calipers / depth gauges maximum measuring range 1000 mm	021000 1000

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Connection cables simplex with data key Type D2	498940 D2
Connection cables simplex with data key Type R2	498940 R2
Connection cables simplex with data key Type USB2	498940 USB2