


DNMG 150612, Grade: IC6015

Order data

Order number	250811 IC6015
GTIN	7291075305159
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Grade	IC6015
Cutting depth a_p	0.5 - 5 mm
Cutting speed v_c main application	140 - 300 m/min
Corner radius	1.2 mm
Cutting conditions	continuous
ISO code indexable insert	DNMG 150612
Chip breaker	M3M
Finishing/roughing assignment	Finishing
Number of changes/inserts	4

Main application	M
Tool material	Carbide
Feed f	0.17 - 0.5 mm/rev.
Manufacturer's designation	DNMG 150612-M3M IC6015
Type of product	Indexable insert for turning