



Digital groove depth gauge IP 67, i-wi, Measuring range: 200mm



Order data

| | |
|--------------|---------------|
| Order number | 418759 200 |
| GTIN | 4059192066147 |
| Item class | 43A |

Description

Version:

For measuring cut-outs, grooves, recesses, shoulders etc. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Very large LCD display with 11 mm character height. Integral i-wi wireless data interface. Measuring beam with double hook. Both contact faces in a single plane.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498940.

i-wi radio receiver No. 498912.

Technical description

| | |
|---|---------------|
| Number of batteries contained | 1 |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032 |
| IP Index of Protection | IP 67 |

| | |
|------------------------------|----------------------------|
| Wireless application | Manufacturer software |
| Measurement deviation E MPE | ± 0.03 mm |
| Calibration | A2 |
| Measuring range | 0 - 200 mm |
| Cross-section measuring beam | 12 × 3.5 mm |
| Reversible reading | mm / inch |
| Power supply | Battery-powered |
| Bridge length | 100 mm |
| Reversible reading | 0.0005 in |
| Reversible reading | 0.01 mm |
| Standard | ISO 13385 |
| Interface | Digimatic interface |
| Interface | MAHR i-wi radio system |
| Interface | USB interface |
| Interface | USB interface |
| Measured value saving | MAHR reference-lock system |
| Measurement technology | digital |
| Material | Stainless steel, INOX |
| Packaging | Wallet |
| Type of product | Groove depth gauge |

Services

| | |
|---|------------|
| Calibration Vernier hook depth gauge maximum measuring range 200 mm | 021220 200 |
| DAkkS calibration Vernier hook depth gauge maximum measuring range 200 mm | 021230 200 |

Accessories

| | |
|--|--------------|
| Radio receivers for Mahr i-wi Type STICK | 498912 STICK |
|--|--------------|

| | |
|---|---------------|
| Radio receiver for Mahr i-wi Type STICK | 498914 STICK |
| Multi-receiver / USB keyboard interface Type | 498975 |
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |