


WNMG 080408, Grade: IC6015

Order data

Order number	251991 IC6015
GTIN	7291075336740
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Main application	M
Finishing/roughing assignment	Finishing
Number of changes/inserts	6
Cutting depth a_p	0.1 - 1.5 mm
Cutting conditions	continuous
Feed f	0.1 - 0.4 mm/rev.
Cutting speed v_c main application	140 - 300 m/min
ISO code indexable insert	WNMG 080408
Chip breaker	F3M
Grade	IC6015

Corner radius	0.8 mm
Tool material	Carbide
Manufacturer's designation	WNMG 080408-F3M IC6015
Type of product	Indexable insert for turning