

**VNMG 160404, Grade: IC6015****Order data**

Order number	251850 IC6015
GTIN	7291075307115
Item class	26B

Description**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

ISO code indexable insert	VNMG 160404
Tool material	Carbide
Chip breaker	M3M
Number of changes/inserts	4
Cutting depth a_p	0.4 - 2.5 mm
Grade	IC6015
Finishing/roughing assignment	Finishing
Main application	M
Cutting speed v_c main application	140 - 300 m/min

Corner radius	0.4 mm
Cutting conditions	continuous
Feed f	0.07 - 0.3 mm/rev.
Manufacturer's designation	VNMG 160404-M3M IC6015
Type of product	Indexable insert for turning