

Yale

Hydraulic lifting wedge HK-16T, Safe working load/Type: 16/1 t



Order data

Order number	086048 16/1
GTIN	4025092485579
Item class	08Y

Description

Version:

All components and attachments satisfy **metric standard ranges**, which considerably simplifies assembly, service, and the procurement of spare parts. **100 % compatibility** with all commercially-available 700 bar hydraulic systems.

Forged lifting wedge with parallel opening stroke and a **very small insertion gap of only 9.5 mm** for connection to a hydraulic system with max. 700 bar operating pressure. Lifting wedge with hydraulic connection and quick coupling.

Application:

For vertical lifting of heavy objects, equipment, and machinery. Maximum lifting force per lifting wedge is 16 t, several lifting wedges can be used if required.

Note:

Closed systems are pre-mounted ex works, filled and air bled.

For hydraulic hand pump see No. 086050, hydraulic hose No. 086081, pressure gauge No. 086087.

Weight: 5 kg

Technical description

Type	1
very small access gap	9.5 mm
Weight	5 kg

maximum lifting force

16 t