

## Garant

### Solid carbide arbor configurable, for cutter head Ø D: 25mm



#### Order data

Order number	212000 25
GTIN	4045197659255
Item class	29W

#### Description

##### Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

**System radial run-out  $\leq 10 \mu\text{m}$**  due to the combination of taper and flat face.

Shank ground to h6 over its entire length – for individual cutting out and cutting to length.

##### Note:

**Maximum milled depth** =  $L_1 + l$ ;  $l$  = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

The shank can also be cut back to  $\varnothing d_{1 \text{ min}}$ .

#### Technical description

for cutter head Ø D	25 mm
Reach $L_1$	45.8 mm
Shank Ø $D_s$ h6	25 mm
minimum available external Ø $d_1$	24.8 mm
recommended tightening torque	35 Nm
Overall length L	198 mm
Series	TopCut
Through-coolant	yes
Type of product	Threaded copy mill arbor

