



## HELISLOT side milling cutter without flange, $\varnothing$ DC / Zeff: 160/7mm



### Order data

Order number	227714 160/7
GTIN	7291075335590
Item class	19D

### Description

#### Version:

Economical machining of grooves and T-slots. Achieve different slot widths with only one insert size thanks to the insert seat concept with staggered teeth formation. Square inserts with positive rake angle for efficient and gentle machining. Very reliable process thanks to optimised insert support in the seat.

#### Spare part:

Pack of insert screws No. **229697 1** (IP15; 4.8 Nm).

### Technical description

Series	HELISLOT
Number of indexable inserts	14
Number of effective inserts $Z_{\text{eff}}$	7
Overall length $L_{\text{tot}}$	20 mm
Slot width $a_p$	16 mm
Cutting edge $\varnothing D_c$	160 mm

Mounting bore $\varnothing$	40 mm
maximum cutting depth $a_{e\ max}$	50.5 mm
Manufacturer's designation	SDN D160-16-40-XN13
Shank type	with bore
Type of product	Side milling cutter

---

## Accessories

Insert screw Type 1	229697 1
---------------------	----------