

Garant

Shoulder mill 90°, with bore, Ø D / number of teeth Z: 40/4mm


Order data

Order number	215715 40/4
GTIN	4045197410603
Item class	210

Description
Version:

Indexable shoulder mill with irregular pitch for very smooth cutting.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 5.0** with bit No. **674252 size 15IP**.

Technical description

Cutting edge Ø D _c	40 mm
Overall length L _{tot}	40 mm
suitable indexable insert	AP.. 16..
Mounting bore Ø	16 mm
Pack of insert screws	219812 (15IP; 5.0 Nm)
Number of cutting edges Z	4
Shank type	with bore
Setting angle κ	90 degrees
Milling application	End milling

Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

Set of insert screws 10-piece	219812
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 5,0 N·m	211750 5,0