

**Garant**
**Chamfer mills, with bore, Angle  $\gamma$ : 60°**

**Order data**

Order number	215795 60
GTIN	4045197383242
Item class	210

**Description**
**Note:**

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

**Technical description**

suitable indexable insert	AP.. 1003
smallest $\varnothing$ D	17 mm
Mounting bore $\varnothing$	16 mm
largest $\varnothing$ D <sub>1</sub>	45 mm
achievable chamfer length l	27.5 mm
Overall length L <sub>tot</sub>	52 mm
Pack of insert screws	219814 (8IP; 1.2 Nm)
achievable chamfer width b	13 mm
Angle $\gamma$	60 degrees
achievable chamfer height h	24 mm
Number of effective inserts Z <sub>eff</sub>	3

Feed rate per tooth at $h_{\max}$	0.12 mm
Number of indexable inserts	9
Shank type	with bore
Through-coolant	yes
Tool exchange	PowerCard
Type of product	Indexable end mill

---

## Accessories

Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2
Set of insert screws 10-piece	219814
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP