



## Indexable milling cutter 90°, with bore, Ø D / number of teeth Z: 125/9\_ mm

### Order data

Order number	215715 125/9_
GTIN	4045197410887
Item class	210

### Description

#### Version:

Indexable face mill with irregular pitch for very smooth cutting.

#### Description:

GARANT end mill 90° with bore

#### Note:

Use GARANT torque screwdriver TQ No. **211750 size 5.0** with bit No. **674252 size 15IP**.

Setting angle  $\kappa$ : 90 degrees

Milling application: End milling

Spacing of the milling cutter's cutting edges: unequal spacing

Through-coolant: true

Tool exchange: PowerCard

### Technical description

Tool exchange	PowerCard
Shank type	with bore
Machining strategy	
Through-coolant	yes
Milling application	End milling
Setting angle $\kappa$	90 degrees
Spacing of the cutters	unequal spacing
Type	
Norm	
Type of product	

