

Garant

Shoulder mill 90°, with bore, Ø D / number of teeth Z: 40/4mm



Order data

Order number	215850 40/4
GTIN	4045197221711
Item class	210

Description

Version:

With bore for screw fixing.

Application:

Universal application in all materials.

· **Angle and slot milling, milling pockets, circular milling, bore milling, peripheral milling.**

Note:

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

· **Change the insert screws after longer use of the indexable inserts. Ensure the insert screws are well greased before use (e.g. with copper paste).**

Technical description

Overall length L_{tot}	40 mm
Cutting edge $\varnothing D_c$	40 mm
Mounting bore \varnothing	16 mm
Pack of insert screws	219814 (8IP; 1.2 Nm)
suitable indexable insert	AP.. 1003..
Number of cutting edges Z	4

Ramping angle α_{\max}	0.41 degrees
Ramping length L for α_{\max}	34.85 mm
Circular interpolation milling $\varnothing D_{\min}$	77 mm
Circular interpolation milling $\varnothing D_{\max}$	78 mm
$\varnothing D_3$	37 mm
Shank type	with bore
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Circular milling
Milling application	Ramping
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Set of insert screws 10-piece	219814