



## Indexable milling cutter 90°, with threaded shank, Ø D / number of teeth Z: 24,7/4\_ mm

### Order data

Order number	215870 24,7/4_
GTIN	4045197195388
Item class	210

### Description

#### Description:

General application in all materials and for slot milling. Arbors for milling cutters with thread see catalogue section 3.

#### Application:

General application in all materials and for slot milling.

#### Note:

Arbors for milling cutters with thread see catalogue section 3.

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

Setting angle  $\kappa$ : 90 degrees

Milling application: Circular milling

Milling application: Ramping

Milling application: End milling

Through-coolant: true

Machining strategy: MTC

### Technical description

Setting angle $\kappa$	90 degrees
Shank type	with threaded shank
Milling application	Circular milling
Milling application	Ramping
Milling application	End milling
Tool exchange	PowerCard
Machining strategy	MTC
Through-coolant	yes

Spacing of the cutters

---

Type

---

Norm

---

Type of product

---