

**CCMT 09T308, Grade: CA510****Order data**

Order number	260098 CA510
GTIN	4960664696482
Item class	25E

Description

CCMT 09T308 CA510 Grade: CA510

Chip breaker: HQ

Tolerance: M

Cutting depth a_p : 0.5 - 2.5 mm

Feed f : 0.05 - 0.25 mm/rev.

Cutting speed v_c main application: 140 - 450 m/min

Technical description

Corner radius	0.8 mm
Cutting conditions	continuous
Main application	P
Cutting speed v_c main application	140 - 450 m/min
Chip breaker	HQ
Cutting depth a_p	0.5 - 2.5 mm
Feed f	0.05 - 0.25 mm/rev.

Grade	CA510
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 09T308
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning