



PENTACUT PCH 24-34 toolholder, right-hand, Shank size / insert size: 25/24mm



Order data

Order number	273924 25/24
GTIN	7291075172089
Item class	26D

Description

Suitable for:

Inserts No. 273937 – 273939.

Technical description

Head length L_1	19.5 mm
Grooving depth t_{max}	6.5 mm
Overall length L	135 mm
Series	PENTACUT
Shank size	25 mm
CWN-CWX	0.5 - 3.2 mm
Manufacturer's designation	PCHR 25-24
Application type	right-hand
Through-coolant	no
axial grooving possible	no
Type of product	Screw-on toolholder

