



PENTACUT PCH 24-34 toolholder, right-hand, Shank size / insert size: 20/34mm



Order data

Order number	273924 20/34
GTIN	7291075287134
Item class	26D

Description

Suitable for:

Inserts No. 273937 – 273939.

Technical description

Grooving depth t_{max}	10 mm
Series	PENTACUT
Overall length L	120 mm
Head length L_1	31 mm
Shank size	20 mm
HBH	6 mm
CWN-CWX	1.5 - 4 mm
Manufacturer's designation	PCHR 20-34
Application type	right-hand
Through-coolant	no
axial grooving possible	no
Type of product	Screw-on toolholder

