



## PENTACUT PCH-17 toolholder, right-hand, Shank size / insert size: 25/17mm



### Order data

Order number	273950 25/17
GTIN	7291075389616
Item class	26D

### Description

#### Application:

For flush work on workpiece shoulders for groove widths of 0.25 mm – 3.18 mm.

#### Suitable for:

Inserts No. 273956 – 273959.

#### Note:

For right-hand toolholders use right-hand inserts, for left-hand toolholders use left-hand inserts.

### Technical description

Series	PENTACUT
Head length $L_1$	17 mm
Grooving depth $t_{max}$	4 mm
Overall length L	120 mm
Shank size	25 mm
OAH	30.6 mm
Insert size	17 mm
Manufacturer's designation	PCHRS 25-17
Application type	right-hand
Through-coolant	no
axial grooving possible	no

Type of product

Screw-on toolholder