

HOLEX**HOLEX Pro INOX solid carbide high-performance drill, plain shank DIN 6535 HB, AlTiN, Ø DC m7: 7,5mm****Order data**

Order number	GG1286 7,5
GTIN	4067263106470
Item class	GGN

Description**Version:**

Efficient drilling especially for use in **stainless and acid-resistant steels**. Straight main cutting edges with **optimised cutting edge design** for improved chip breaking behaviour. Enlarged flutes for **excellent chip evacuation**. Increased wear resistance due to **improved carbide substrate** and **high temperature resistant coating**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Number of cutting edges Z	2
Nominal Ø D_c	7.5 mm
Overall length L	91 mm
Standard	DIN 6537
Tolerance nominal Ø	m7
Flute length L_c	53 mm

Shank $\varnothing D_s$	8 mm
Contents	5
Feed f in stainless steel $< 900 \text{ N/mm}^2$	0.1 mm/rev.
recommended maximum drilling depth L_2	41.8 mm
Series	Pro Inox
Coating	AlTiN
Tool material	Solid carbide
Version	6xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Colour ring	blue
Type of product	Twist Drill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu $> 10\% \text{ Si}$	suitable only under restricted conditions	120 m/min	N
Steel $< 500 \text{ N/mm}^2$	suitable	120 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	110 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	80 m/min	P
INOX $< 900 \text{ N/mm}^2$	suitable	55 m/min	M
INOX $> 900 \text{ N/mm}^2$	suitable	45 m/min	M
Ti $> 850 \text{ N/mm}^2$	suitable	35 m/min	S
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

Accessories

HOLEX Pro Inox solid carbide high-performance drill, plain shank
DIN 6535 HA Ø DC m7 7,5 mm

122685 7,5