



DN.G 110408, Grade: HB7140

Order data

Order number	250754 HB7140
GTIN	4045197663269
Item class	21G

Description

DN.G 110408 HB7140 Grade: HB7140
 Chip breaker: V4M
 Tolerance: M
 Cutting depth a_p : 1 - 5 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 85 - 210 m/min

Technical description

Indexable insert clearance angle	degrees
Product name attribute	
Insert assignment	
Rake	degrees
Shim	
Indexable insert profile	neutral
Type of product	