

**DN.G 150608, Grade: HB7010****Order data**

| | |
|--------------|---------------|
| Order number | 250762 HB7010 |
| GTIN | 4045197663399 |
| Item class | 21G |

Description

DN.G 150608 HB7010 Grade: HB7010
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 110 - 280 m/min

Technical description

| | |
|----------------------------------|---------|
| Indexable insert clearance angle | degrees |
| Product name attribute | |
| Insert assignment | |
| Rake | degrees |
| Shim | |
| Indexable insert profile | neutral |
| Type of product | |