



MINCUT boring bar, right-hand, Shank \varnothing / insert size: 12/10mm



Order data

Order number	270420 12/10
GTIN	7291075262407
Item class	26l

Description

Version:

- Carbide insert screwed on to the end face, positive force transmission due to end face serrations.
- Insert change is very easy to perform.

Application:

For face grooving and groove turning in the diameter range 8 mm – 17 mm.

Suitable for:

Inserts No. 270422 – 270429.

Technical description

Centre offset L_3	11.2 mm
Series	MINCUT
Overall length L	90 mm
Shank $\varnothing D_s$	12 mm
Insert size	10 mm
Head length l_2	17.2 mm
Function width f_1	2.4 mm
Radial width f_2	5.5 mm
Cooling $\varnothing d_5$	6 mm
Radius R	4.6 mm
Manufacturer's designation	MIFHR 12C-10

Application type	right-hand
Through-coolant	yes
Type of product	Boring bar