



MINCUT boring bar, right-hand, Shank \varnothing / insert size: 20/15mm



Order data

Order number	270420 20/15
GTIN	7291075262438
Item class	26l

Description

Version:

- Carbide insert screwed on to the end face, positive force transmission due to end face serrations.
- Insert change is very easy to perform.

Application:

For face grooving and groove turning in the diameter range 8 mm – 17 mm.

Suitable for:

Inserts No. 270422 – 270429.

Technical description

Series	MINCUT
Overall length L	100 mm
Insert size	15 mm
Centre offset L_3	12.5 mm
Shank $\varnothing D_s$	20 mm
Head length l_2	19 mm
Function width f_1	4.7 mm
Radial width f_2	9 mm
Cooling $\varnothing d_5$	8.5 mm
Radius R	11.3 mm

Manufacturer's designation	MIFHR 20C-15
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar