



## MINCUT boring bar, right-hand, Shank $\varnothing$ / insert size: 10/8mm



### Order data

Order number	270420 10/8
GTIN	7291075262384
Item class	26l

### Description

#### Version:

- Carbide insert screwed on to the end face, positive force transmission due to end face serrations.
- Insert change is very easy to perform.

#### Application:

For face grooving and groove turning in the diameter range 8 mm – 17 mm.

#### Suitable for:

Inserts No. 270422 – 270429.

### Technical description

Shank $\varnothing$ D <sub>s</sub>	10 mm
Centre offset L <sub>3</sub>	7.4 mm
Insert size	8 mm
Overall length L	102.5 mm
Series	MINCUT
Head length l <sub>2</sub>	12.5 mm
Radial width f <sub>2</sub>	4.5 mm
Function width f <sub>1</sub>	1.4 mm
Cooling $\varnothing$ d <sub>5</sub>	5 mm
Radius R	3.8 mm
Manufacturer's designation	MIFHR 10C-8

Application type	right-hand
Through-coolant	yes
Type of product	Boring bar