HOLEX

VNMG 160404 Set 10 pieces, Grade: HBX130

Order data

Order number	251832 HBX130
GTIN	4045197665133
Item class	22D

Description

VNMG 160404 Set of 10 pieces HBX130 Grade: HBX130
Chip breaker: MM
Cutting depth a_p: 0.75 - 4 mm
Feed f: 0.08 - 0.35 mm/rev.
Cutting speed v_c main application: 60 - 200 m/min

Technical description

Cutting depth a_p	0.75 - 4 mm
Chip breaker	MM
Cutting speed v_c main application	60 - 200 m/min
Cutting conditions	slightly interrupted
Corner radius	0.4 mm
Feed f	0.08 - 0.35 mm/rev.
Main application	M

Grade	HBX130
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	VNMG 160404
Number of changes/inserts	4
Type of product	Indexable insert for turning