

Garant**CC.T 120408, Grade: HU7310**

Order data

Order number	260160 HU7310
GTIN	4045197668554
Item class	21G

Description

Technical description

Chip breaker	AM
Cutting speed v_c main application	350 - 600 m/min
Cutting depth a_p	0.1 - 4 mm
Main application	N
Cutting conditions	continuous
Feed f	0.05 - 0.5 mm/rev.
Corner radius	0.8 mm
Grade	HU7310
Finishing/roughing assignment	Finishing
Tool material	Carbide

Coating	uncoated
ISO code indexable insert	CCMT 120408
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning