

Garant**Torque screwdriver, fixed setting, set torque: 0,6N·m**

Order data

Order number	211750 0,6
GTIN	4045197552372
Item class	21B

Description

Version:

Torque screwdriver with easy-grip 2-component T-handle. The torque is fixed. Toolholder with permanent magnet.

Function:

When the torque is reached the screwdriver triggers **with clearly audible and perceptible signal**. The long-travel indication gives the user an unmistakable signal that the set torque has been reached.

Application:

In conjunction with **1/4 inch bits** with **C 6.3** or **E 6.3 shank**, e.g. **Torx Plus® bit No. 674252**. Ideal for precise tightening of indexable inserts to the specified torque.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

Supplied **without** bit.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Blade length	50 mm
Torque measuring accuracy	±15 %
set torque	0.6 Nm
Bit socket	D 6,3
Bit socket	F 6.3
Standard	DIN EN ISO 6789
Adjustable trigger value	non-adjustable
Trigger principle	Mechanical long travel release
Overall length L	107 mm
Setting the trigger value	preset
Feedback	triggering
Measurement process	Torque
Connection format	Bit holder 1/4 inch
Reversible reading	Nm
Direction of tightening	Right-hand tightening
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------

Accessories

"TQ-Station" – storage station for torque screwdrivers	659964
--	--------