

Garant
CC.T 09T308, Grade: HB7310


Order data

Order number	260152 HB7310
GTIN	4045197668196
Item class	21G

Description

Technical description

Cutting speed v_c main application	350 - 600 m/min
Cutting conditions	continuous
Main application	N
Chip breaker	AM
Feed f	0.05 - 0.5 mm/rev.
Corner radius	0.8 mm
Cutting depth a_p	0.1 - 4 mm
Grade	HB7310
Finishing/roughing assignment	Finishing
Tool material	Carbide

ISO code indexable insert	CCMT 09T308
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning