

Garant
Clamping toolholder, left-hand, Shank / insert size: 25/16mm

Order data

Order number	251009 25/16
GTIN	4045197650689
Item class	21T

Technical description

ISO code toolholder	CKJNR/L 2525M16
Clamp	259038 17
Shank size	25 mm
Head length L ₁	32 mm
Shim	259031 6
Shim pins pack	259044 3
Spring	259046 3
suitable indexable insert	KNUX 1604.. R/L
Insert size	16 mm
Screw for clamp	259021 3
Functional width L ₄	32 mm
Overall length L	150 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw Type 17	259038 17
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4
Set of shim pins 10 pieces Type 3	259044 3
Screw for clamping claw Type 3	259021 3
Spring Type 3	259046 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Shim Type 6	259031 6
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600