


KOMET KUB Centron® Powerline drill head, Ø DC: 33,2mm

Order data

Order number	236651 33,2
GTIN	4047109226920
Item class	24L

Description
Version:

The drill point guides the tool precisely on the axis of the hole, thus ensuring both straightness and very high process reliability, with stability in hole depths up to 9×D.

Spot drilling on flat level surfaces without a pilot hole.

Drill head without slide bars and slide bar adjustment.

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

With centring tip No. 236659.

With indexable inserts No. 236520 – 236576.

Note:

Further sizes available on request.

Technical description

Number of cutting edges Z	2
Screw for base body	239653 15IP
ISO code indexable insert	SOEX 110508
Pack of insert screws	239652 15IP2 (2.8 Nm)
Centring tip size	50
Base body size	33

Series	KUB Centron®
Nominal Ø D	33.2
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	Drilling blind holes
Through-coolant	yes
Type of product	Indexable drill

Accessories

Torx Plus® insert screw set 10 pieces Drive 15IP	239652 15IP
Torx Plus® insert screw set 10 pieces Drive 15IP	239653 15IP
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 2,8 N·m	211750 2,8