

Yale

Electric chain hoist CPV VEGO, Type: 0,5-8



Order data

Order number	086035 0,5-8
GTIN	2050001790583
Item class	08Y

Description

Version:

Electric chain hoist with **lifting hook** in robust and reliable design. The integral **end-of-travel switch** for the highest and lowest hook positions protects the clutch, motor, and housing and extends their working life. Drive group 1 Am, 50 % duty cycle at one speed, standard operating voltage (400 V / 50 Hz). Enhanced operating safety due to 42 V contactor controls, encapsulated control switches to Index of Protection IP65, motors to IP55.

Note:

Versions with 2 speeds (precision lifting) and other lifting heights, power traverse, chain box and radio and 230 V power supply available on request.

Technical description

adjustable slip clutch	yes
Type	0,5-8
Drive group to FEM/ISO	1AM
Number of chains	1

Safe working load	500 kg
Safe working load in t	0.5 t
Lifting speed	8 m/min
Standard lifting height	3 m
automatic cut-out at the end	yes
Weight	26 kg
Type of product	Lever hoist