

**Garant**
**QuickTurn clamping toolholder, left-hand, Shank / insert size: 25/08mm**

**Order data**

Order number	251907 25/08
GTIN	4045197558299
Item class	21U

**Description**
**Advantage:**

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Through-coolant: no

ISO code toolholder: DWLNR/L 2525M08

suitable indexable insert: WN.. 0804..

Functional width L<sub>4</sub>: 32 mm

Head length L<sub>1</sub>: 32 mm

Overall length L: 150 mm

Shim: 259031 42

**Technical description**

Clamp	259038 10
Shim screw	259025 4
suitable indexable insert	WN.. 0804..
Shim	259031 42
Functional width L <sub>4</sub>	32 mm
Insert size	8 mm
Shank size	25 mm

Head length L <sub>1</sub>	32 mm
ISO code toolholder	DWLNR/L 2525M08
Overall length L	150 mm
Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	95 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

Clamping claw Type 10	259038 10
Shim screw	259171
Clamping claw	259354
Shim	259581
Shim screw Type 4	259025 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 42	259031 42
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500