



Digital groove depth gauge IP 67, i-wi, Measuring range: 300mm



Order data

Order number	418759 300
GTIN	4059192066154
Item class	43A

Description

Version:

For measuring cut-outs, grooves, recesses, shoulders etc. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Very large LCD display with 11 mm character height. Integral i-wi wireless data interface. Measuring beam with double hook. Both contact faces in a single plane.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498940.

i-wi radio receiver No. 498912.

Technical description

Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Cross-section measuring beam	12 × 3.5 mm
Bridge length	150 mm
IP Index of Protection	IP 67

Reversible reading	0.01 mm
Reversible reading	0.0005 in
Reversible reading	mm / inch
Calibration	A2
Power supply	Battery-powered
Measuring range	0 - 300 mm
Wireless application	Manufacturer software
Measurement deviation E MPE	±0.04 mm
Standard	ISO 13385
Interface	Digimatic interface
Interface	MAHR i-wi radio system
Interface	USB interface
Interface	USB interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Material	Stainless steel, INOX
Packaging	Wallet
Type of product	Groove depth gauge

Services

DAkkS calibration Vernier hook depth gauge maximum measuring range 300 mm	021230 300
Calibration Vernier hook depth gauge maximum measuring range 300 mm	021220 300

Accessories

Multi-receiver / USB keyboard interface Type	498975
Radio receivers for Mahr i-wi Type STICK	498912 STICK
Radio receiver for Mahr i-wi Type STICK	498914 STICK

Button cell / special battery Battery type CR2032

081560 CR2032