

Garant
Clamping toolholder, right-hand, Shank / insert size: 32/16mm

Order data

Order number	251008 32/16
GTIN	4045197654632
Item class	21T

Technical description

Shim pins pack	259044 3
Insert size	16 mm
Shim	259031 4
Shank size	32 mm
Functional width L ₄	40 mm
Clamp	259038 16
Screw for clamp	259021 3
suitable indexable insert	KNUX 1604.. R/L
Head length L ₁	32 mm
ISO code toolholder	CKJNR/L 3232P16
Spring	259046 3
Overall length L	170 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of shim pins 10 pieces Type 3	259044 3
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4
Clamping claw Type 16	259038 16
Shim Type 4	259031 4
Screw for clamping claw Type 3	259021 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Spring Type 3	259046 3
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600