

**KNUX 160410L, Grade: HB7135****Order data**

Order number	251038 HB7135
GTIN	4045197676351
Item class	21G

**Description**

KNUX 160410L HB7135 Chip breaker: VM  
Chip diverter: 2.2 mm  
Cutting depth  $a_p$ : 0.5 - 4 mm  
Feed  $f$ : 0.2 - 0.5 mm/rev.  
Cutting speed  $v_c$  main application: 55 - 140 m/min

**Technical description**

ISO code indexable insert	KNUX 160410L
Insert assignment	left-hand
Type of product	